
Manual Table Top Tray Sealers




Description

Lower the handle to apply seal pressure to seal the tray.

- Photo eye included for printed film
- Stainless steel construction
- Cannot change tooling
- 110 Volt power
- Will run APET, CPET, PP, PET or PE trays
- No air required all electric operation
- Film is die cut around tray
- Lidding film and trays available upon request

















- · Model: PP-YTB-190
- · Maximum tray height: 140mm (5.5")
- · Maximum tray length×width:

sealing 1 at a time: 190×190 (7.5" x 7.5") sealing 2 at a time: 190×80 (7.5" x 3.15") sealing 4 at a time: 80×80 (3.15" x 3.15")

- · Cycle time: 6 seconds
- · Voltage: AC220V/AC110V
- Machine dimensions (mm): 310×400×580
- · Machine dimensions (in): 12" x 15.7" x 23"
- Weight: ≈50kg (110 lbs)
- Max Film diameter: Φ220mm (8.6")
- Total power: ≈1.5kw

- Model: **PP-YTB-280**
- · Maximum tray height: 140mm (5.5")
- · Maximum tray length×width:

sealing 1 at a time: 280×280 (11" x 11") sealing 2 at a time: 280×125 (11" x 4.92") sealing 4 at a time: 125×125 (4.9" x 4.9")

- · Cycle time: 6 seconds
- · Voltage: AC220V/AC110V
- Machine dimensions (mm): 390×400×580
- Machine dimensions (in): 15.3" x 15.75" x 22.8"
- Weight: ≈60kg (132 lbs)
- Max Film diameter : Φ220mm (8.6")
- Total power: ≈2.0kw